



LOC153222 Antibody

CATALOG NUMBER: 27-525



Antibody used in WB on Human Lung at
0.2-1 ug/ml.

Specifications

SPECIES REACTIVITY:	Dog, Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, WB
APPLICATIONS:	LOC153222 antibody can be used for detection of LOC153222 by ELISA at 1:12500. LOC153222 antibody can be used for detection of LOC153222 by western blot at 0.5 ug/mL, and HRP conjugated secondary antibody should be diluted 1:50,000 - 100,000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
POSITIVE CONTROL:	1) Cat. No. XBL-10410 - Fetal Lung Tissue Lysate
PREDICTED MOLECULAR WEIGHT:	47 kDa
IMMUNOGEN:	Antibody produced in rabbits immunized with a synthetic peptide corresponding a region of human LOC153222.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Antibody is purified by peptide affinity chromatography method.
PHYSICAL STATE:	Lyophilized
BUFFER:	Antibody is lyophilized in PBS buffer with 2% sucrose. Add 50 uL of distilled water. Final antibody concentration is 1 mg/mL.
CONCENTRATION:	1 mg/ml
STORAGE CONDITIONS:	For short periods of storage (days) store at 4°C. For longer periods of storage, store LOC153222 antibody at -20°C. As with any antibody avoid repeat freeze-thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	LOC153222, LRF, C5orf41
ACCESSION NO.:	Q86YR3
PROTEIN GI NO.:	74714190

OFFICIAL SYMBOL: CREBRF

GENE ID: 153222

Background

BACKGROUND: The LOC153222 gene is similar to hypothetical protein.

FOR RESEARCH USE ONLY

December 12, 2016